

## rational Sample Divider

Gives a homogeneous and representative dividing of grain samples.



### Advantages:

1. Made of stainless steel, no static electricity.
2. The construction prevents the escape of dust.
3. The hinged container prevents failure in operation.
4. The divider is made without any loose parts. Operator friendly.

### Operation:

Pour the sample into the hinged container and tip. If the sample is still too big, repeat with the contents from one of the drawers.



	No of split	Dim of split	max. sample	Dimension	Weight
Mod. 3 .....	10	20 mm	3 l	340x250x210	5 kg
Mod. 10 .....	10	28 mm	10 l	520x330x300	15 kg

Manufacturer:  
**A/S Rational Kornservice**

Gammelby Møllevej 4  
DK-6700 Esbjerg  
Denmark  
Phone: 45 75 12 25 88  
Telefax: 45 75 12 90 89  
Telex: 54 351 rako dk

Agent: